

**Accessories**  
**G 25/4.00A/F BR****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	G 25/4.00A/F BR
Order No.	<a href="#">0192800000</a>
Version	Active components, Fuse
GTIN (EAN)	4008190115319
Qty.	10 pc(s).

**Accessories**  
**G 25/4.00A/F BR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	5 mm	Width (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	1.4 g		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Material data**

Colour	Light Grey
--------	------------

**System specifications**

Version	Fuse accessories
---------	------------------

**Fuse cartridges**

Cartridge fuse	G-Si. 5 x 25	Characteristics	quick-acting
Colour	Light Grey	Colour of the indicator	brown
Current	4 A	Melting integral	40 A <sup>2</sup> s
Power output (@ 1.5 In)	1.3 W	Rated breaking capacity	1.5 kA
Version	Fuse accessories	Voltage drop	180 mV

**Rating data**

Rated voltage	250 V	Rated current	4 A
---------------	-------	---------------	-----

**Classifications**

ETIM 3.0	EC000035	ETIM 4.0	EC000035
ETIM 5.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-90	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
--------------------	-------------------------------------