

THM
THM UR20 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S, S7-300 and S7-400 modules from Siemens.

- The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer.
- Labels can be easily separated
- The THM Plus S printer ensures highly-resistant printing

General ordering data

Type	THM UR20 WS
Order No.	1429420000
Version	THM, Insert markers, 90 x 8 mm, white
GTIN (EAN)	4050118233858
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM
THM UR20 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	8 mm	Width (inches)	0.315 inch
Height	90 mm	Height (inches)	3.543 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	376 g		

General data

Approval acc. to UL 969	No	Colour	white
Halogen	Yes	Material	Vinyl film
Number per roll	1,000	Number per sheet	1,000
Operating temperature range	-40...80 °C	Printing method	Thermotransfer
UL 94 flammability rating	HB	Width	8 mm

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT_U_REMOTE_16/17_EN
Engineering Data	EPLAN_WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

Data sheet

THM
THM UR20 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings