

**cable lug, terminal end
KQIG-M6/-2,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Insulated forked-cable connector made from PVC
or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	KQIG-M6/-2,5
Order No.	1491260000
Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ²
GTIN (EAN)	4050118301182
Qty.	100 pc(s).

cable lug, terminal end KQIG-M6/-2,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	1.214 g
------------	---------

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Connection length (l)	22 mm	Hole	C 6
Identification colour	blue	Inside diameter of collar (d4)	4.5 mm
Inside diameter of flange (d2)	6.5 mm	Inside diameter of shaft (d1)	2.3 mm
Insulation	Available	Material/plastic	PC
Outside diameter of shaft (d3)	11 mm		

Classifications

ETIM 5.0	EC001059	ETIM 6.0	EC001059
eClass 6.2	27-40-02-90	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-40-02-92
eClass 9.1	27-40-02-12		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end KQIG-M6/-2,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

