

CAN SUB-D SK35 TERM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Type	CAN SUB-D SK35 TERM
Order No.	1550600000
Version	
GTIN (EAN)	4050118357073
Qty.	1 pc(s).

CAN SUB-D SK35 TERM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	100 g
------------	-------

Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical specifications for sub-D connector

BUS interface	D-Sub 9-pole, Socket	BUS, cable interface	Screw connection
Data rate	1 Mbps	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Interlock	UNC4-40
Outgoing elbow	35°	Plugging cycles	≥ 200
Protection degree	IP30	Temperature range of housing	-20...+70 ° C
Terminating resistor available	Yes		

Classifications

ETIM 5.0	EC002640	ETIM 6.0	EC001132
eClass 6.2	27-26-07-07	eClass 7.1	27-44-03-07
eClass 8.1	27-44-03-07	eClass 9.0	27-44-03-02
eClass 9.1	27-44-03-90		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
--------------------	-----------------------------------