

**THM
THM MT30X 20/10 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Type	THM MT30X 20/10 WS
Order No.	2556240000
Version	THM, Device markers, 10 x 20 mm, white
GTIN (EAN)	4050118567625
Qty.	10,000 pc(s).
compatible printer	2430920000 2448870000

THM
THM MT30X 20/10 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	20 mm	Width (inches)	0.787 inch
Height	10 mm	Height (inches)	0.394 inch
Net weight	0.038 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester	Number per roll	10,000
Operating temperature range	-40...150 °C	Printing method	Thermotransfer
UL 94 flammability rating	V-0	Version	Self-adhesive, halogen-free
Width	20 mm		

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

Approvals

ROHS	Conform
------	---------

THM THM MT30X 20/10 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

