

**CRIMPFIX R VARIO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Type	CRIMPFIX R VARIO
Order No.	<a href="#">258000000</a>
Version	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4050118605846
Qty.	1 pc(s).

## CRIMPFIX R VARIO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Dimensions and weights

Width	335 mm	Width (inches)	13.189 inch
Height	565 mm	Height (inches)	22.244 inch
Depth	485 mm	Depth (inches)	19.094 inch
Net weight	25,265 g		

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Technical data

Electrical connection	100 - 240 V / 50/60 Hz / 16 VA
-----------------------	-----------------------------------

### PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5.5 bar	Consumables	Linked wire-end ferrules
Crimping	Trapezoidal	Crimping length	8/10 mm
Drive	Electropneumatic	Electrical connection	100 - 240 V / 50/60 Hz / 16 VA
Insertion length, min.	27 mm	Length of wire-end ferrule	14/16 mm
Pulse time	approx. 2 s	Stripping range	0.5 - 2.5 mm <sup>2</sup> (~ AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>

### Classifications

ETIM 6.0	EC002778	eClass 6.2	17-13-01-01
eClass 9.0	17-13-01-01	eClass 9.1	17-13-01-01

### Approvals

ROHS	Conform
------	---------

### Downloads

User Documentation	<a href="#">Manual</a>
--------------------	------------------------