

**Cabtite (cable entry system)
CABTITE CR 24/10 EMV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Cabtite cable entry system offers maximum flexibility in the cable management of control cabinets, enclosures and machines, while at the same time saving time, as well as providing secure sealing and strain relief for pre-terminated and non-terminated cables. Cabtite's modular design of frame, grid inlays and sealing elements enables rapid configuration of cut-outs for pre-terminated cables - without the use of tools and with a reliable sealing of IP66 according to DIN EN 60529. Frame. Inlay. Sealing element. Three basic components in the modular system guarantee highest flexibility, variability and diversity of variants.

General ordering data

Type	CABTITE CR 24/10 EMV
Order No.	2583890000
Version	Cable protection strips, Cabtite (cable entry system), Steel, galvanized, silver, Height: 16 mm, Width: 35.23 mm, Depth: 16 mm
GTIN (EAN)	4050118647068
Qty.	10 pc(s).

Cabtite (cable entry system) CABTITE CR 24/10 EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	140 mm	Length (inches)	5.512 inch
Width	35.23 mm	Width (inches)	1.387 inch
Height	16 mm	Height (inches)	0.63 inch
Depth	16 mm	Depth (inches)	0.63 inch
Mounting dimension - width	5.3 mm	Mounting dimension - height	5.91 mm
Net weight	46.96 g	Diameter	5.3 mm

General information

Halogen	No	Silicone	No
Material	Steel, galvanized		

Classifications

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------