

**THM**  
**THM WO VIN 24.5/100 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

|                    |                                                                   |
|--------------------|-------------------------------------------------------------------|
| Type               | THM WO VIN 24.5/100 WS                                            |
| Order No.          | <a href="#">1391430000</a>                                        |
| Version            | THM, Conductor and cable markers, 8 - 23 mm, 24.5 x 100 mm, white |
| GTIN (EAN)         | 4050118191714                                                     |
| Qty.               | 1 pc(s).                                                          |
| compatible printer | <a href="#">2430920000</a> <a href="#">2448870000</a>             |

# THM

## THM WO VIN 24.5/100 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Technical data

#### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 100 mm   | Width (inches)  | 3.937 inch |
| Height     | 24.5 mm  | Height (inches) | 0.965 inch |
| Depth      | 0.065 mm | Depth (inches)  | 0.003 inch |
| Net weight | 994 g    |                 |            |

#### General data

|                             |                       |                           |              |
|-----------------------------|-----------------------|---------------------------|--------------|
| Adhesive                    | Polyacrylate adhesive | Approval acc. to UL 969   | No           |
| Colour                      | white                 | Halogen                   | Yes          |
| Material                    | Vinyl film            | Number per roll           | 2,000        |
| Operating temperature range | -40...80 °C           | Size of labelling field   | 25 x 24.5 mm |
| Type of printing            | neutral               | UL 94 flammability rating | V-0          |
| Version                     | Self-adhesive         | Width                     | 100 mm       |

#### Conductor and cable markers

|                               |                      |                               |                    |
|-------------------------------|----------------------|-------------------------------|--------------------|
| Conductor O.D.                | 8 - 23 mm            | Conductor O.D., max.          | 23 mm              |
| Conductor O.D., min.          | 8 mm                 | Conductor cross-section, max. | 95 mm <sup>2</sup> |
| Conductor cross-section, min. | 0.75 mm <sup>2</sup> | Halogen                       | Yes                |

#### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001530    | ETIM 6.0   | EC001530    |
| eClass 6.2 | 27-40-04-01 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-29 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 |            |             |

#### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

#### Downloads

|                  |                                                |
|------------------|------------------------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a>                   |
| Engineering Data | <a href="#">STEP</a>                           |
| Software         | <a href="#">M-Print PRO configuration file</a> |

### THM THM WO VIN 24.5/100 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

