

**CMA-Series
CMA-31-250-5A-5VA-0,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The pluggable current transformers are particularly suitable for installation on the busbar.

Advantages:

- Screwless connection system with tension-clamp terminal.
- Time-saving connection option for solid and flexible conductors.
- Shock-proof and resistant to vibration, high mechanical retention forces.
- High current resistance

General ordering data

Type	CMA-31-250-5A-5VA-0,5
Order No.	1482050000
Version	Primary current: 250 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 0,5
GTIN (EAN)	4050118291094
Qty.	1 pc(s).

CMA-Series
CMA-31-250-5A-5VA-0,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	60 mm	Width (inches)	2.362 inch
Height	80.9 mm	Height (inches)	3.185 inch
Depth	52 mm	Depth (inches)	2.047 inch
Net weight	315 g		

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-5 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-25 °C
Operating temperature	-5 °C...50 °C	Storage temperature	-25 °C...70 °C

Technical data

Insulation class	E	Nominal frequency	50 Hz
Operating voltage $U_{\max}$, max.	1,2 kV	Thermal rated continuous current I_{thermal}	1.2 x I_{rated}

Dimensions of live conductors

Rail	20 x 20 mm, 25 x 12 mm, 30 x 10 mm	Round conductor	25.7 mm
------	---------------------------------------	-----------------	---------

Electrical attributes

Load	5 VA	Primary current	250 A
Secondary current max.	5 A	Tolerance class	0,5

Classifications

ETIM 5.0	EC002048	ETIM 6.0	EC002048
eClass 6.2	27-21-09-02	eClass 7.1	27-21-09-02
eClass 8.1	27-21-09-02	eClass 9.0	27-21-09-02
eClass 9.1	27-21-09-02		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	3D drawing
User Documentation	instruction sheet english.pdf Betriebsanleitung deutsch

CMA-Series CMA-31-250-5A-5VA-0,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

