

**Cabtite (cable entry system)**  
**CABTITE GI H BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The pluggable click inlays allow the frame openings to be configured as required for use with small or large sealing elements. An audible "click" confirms correct installation. This means that the Cabtite cable entry system can be variably configured for different requirements (cables, conductors, hoses, pneumatic and hydraulic lines).

**General ordering data**

|            |                                                                                                                                                          |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type       | CABTITE GI H BK                                                                                                                                          |
| Order No.  | <a href="#">2584270000</a>                                                                                                                               |
| Version    | grid inlay, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 17.5 mm, Width: 44 mm, Depth: 17.5 mm, -40 °C... 120 °C |
| GTIN (EAN) | 4050118617122                                                                                                                                            |
| Qty.       | 5 pc(s).                                                                                                                                                 |

## Cabtite (cable entry system) CABTITE GI H BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Length                   | 67 mm      | Length (inches) | 2.638 inch |
| Width                    | 44 mm      | Width (inches)  | 1.732 inch |
| Height                   | 17.5 mm    | Height (inches) | 0.689 inch |
| Height of lowest version | 17.5 mm    | Depth           | 17.5 mm    |
| Depth (inches)           | 0.689 inch | Net weight      | 9.61 g     |

### General information

|                           |                                   |         |     |
|---------------------------|-----------------------------------|---------|-----|
| UL 94 flammability rating | V-0                               | Halogen | No  |
| Silicone                  | No                                | Sealing | TPE |
| Material                  | Polyamide, glass fibre-reinforced |         |     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC002624    | eClass 6.2 | 27-14-92-01 |
| eClass 9.0 | 27-18-28-15 | eClass 9.1 | 27-18-92-65 |

### Approvals

Approvals



ROHS Conform

### Downloads

|                    |                                                   |
|--------------------|---------------------------------------------------|
| Engineering Data   | <a href="#">STEP</a>                              |
| User Documentation | <a href="#">Cabtite Installation Instructions</a> |