SAIE-M8B-8-0.2U-FP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M8B-8-0.2U-FP
Order No.	1467630000
Version	Built-in plugs, M8 thread, Female socket, straight, M 8, No. of poles: 8
GTIN (EAN)	4050118273373
Qty.	1 pc(s).

SAIE-M8B-8-0.2U-FP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	10 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Standards

Connector standard	IEC 61076-2-104

General data

Cable glands	M 8	Coding	none
Conductor O.D.	-	Connection thread	M8 thread
Contact surface	Gold-plated	Core cross-section	0.14 mm²
Housing main material	Brass, nickel-plated	No. of poles	8
Protection degree	IP67, when screwed in	Rated current	1.5 A
Rated voltage	30 V	Rated voltage (text)	30 V
Strand / cable length	0.2 m	Temperature range of housing	-25...+85 °C
Type of connection	Socket connector		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002635
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

Approvals

Approvals	
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	STEP

SAIE-M8B-8-0.2U-FP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

