

THM
THM MT30X 16.5/5.1 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Type	THM MT30X 16.5/5.1 GE
Order No.	1516990000
Version	THM, Device markers, 5.1 x 16.5 mm, yellow
GTIN (EAN)	4050118324655
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM

THM MT30X 16.5/5.1 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	16.5 mm	Width (inches)	0.65 inch
Height	5.1 mm	Height (inches)	0.201 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	228 g		

General data

Adhesive	Acrylate	Colour	yellow
Halogen	No	Material	Polyester
Number per roll	10,000	Operating temperature range	-40...150 °C
Printing method	Thermotransfer	UL 94 flammability rating	V-0
Version	Self-adhesive, halogen-free	Width	16.5 mm

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

THM
THM MT30X 16.5/5.1 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings