

**SwitchMark  
SM 37.5/17 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet PRO, MCP Plus plotter, MCP Basic or MC-Mobilo marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

| Type               | SM 37.5/17 MC NE WS                             |
|--------------------|-------------------------------------------------|
| Order No.          | <a href="#">1336710000</a>                      |
| Version            | SwitchMark, Device markers, 17 x 37.5 mm, white |
| GTIN (EAN)         | 4050118141269                                   |
| Qty.               | 40 pc(s).                                       |
| compatible printer | <a href="#">1324380000</a>                      |

## SwitchMark SM 37.5/17 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 37.5 mm | Width (inches)  | 1.476 inch |
| Height     | 17 mm   | Height (inches) | 0.669 inch |
| Depth      | 1.2 mm  | Depth (inches)  | 0.047 inch |
| Net weight | 1.96 g  |                 |            |

### General data

|                           |              |                             |               |
|---------------------------|--------------|-----------------------------|---------------|
| Colour                    | white        | Halogen                     | No            |
| Material                  | Polyamide 66 | Operating temperature range | -40... 100 °C |
| UL 94 flammability rating | V-2          | Width                       | 37.5 mm       |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001288    | ETIM 6.0   | EC001288    |
| eClass 6.2 | 27-37-12-25 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-29 | eClass 9.0 | 27-40-06-29 |
| eClass 9.1 | 27-40-06-29 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
| Engineering Data | <a href="#">STEP</a>         |

### SwitchMark SM 37.5/17 MC NE WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

