

**OMNIMATE Signal - series BL/SL 5.08
BLZP AH 12 BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Effective protection, optimised ergonomics and closed design:**

From the strain relief on the connected conductors and the visual/contact protection and the disconnection aid: the optional retrofit hoods perform mechanical, visual and haptic functions.

The two half shells clip together securely, enclose the plug completely and offer the following functions:

- Cable ties or integrated cable clips provide strain relief.
- Marked with dekafix labels or adhesive strips
- Mounting side by side without losing poles or displacing the pitch
- Compatible: suitable for plugs with or without a flange or mounting bracket
- Flexible: 1-3 cable outlets leading in different directions available depending on the size

Weidmüller hoods offer added stability, better identification, complete compatibility and versatility. The result: maximum reliability and user-friendliness in any application.

General ordering data

Type	BLZP AH 12 BK
Order No.	2507140000
Version	PCB plug-in connector, Accessories, black, No. of poles: 12
GTIN (EAN)	4050118524406
Qty.	10 pc(s).
Product data	
Packaging	Box

OMNIMATE Signal - series BL/SL 5.08 BLZP AH 12 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	60 mm	Length (inches)	2.362 inch
Width	19 mm	Width (inches)	0.748 inch
Height	48 mm	Height (inches)	1.89 inch
Net weight	21.1 g		

Material data

Insulating material	PBT	Colour	black
Colour chart (similar)	RAL 9011	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984
-------------------------	------------------------

Packing

Packaging	Box	VPE length	160 mm
VPE width	105 mm	VPE height	50 mm

Classifications

ETIM 4.0	EC000250	ETIM 5.0	EC000250
ETIM 6.0	EC002638	eClass 6.2	27-26-92-01
eClass 9.0	27-44-03-09	eClass 9.1	27-44-03-09

Notes

Notes	
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Approvals

ROHS	Conform
------	---------

OMNIMATE Signal - series BL/SL 5.08 BLZP AH 12 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

