

THM
THM WO 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Type	THM WO 24.5/100 WS
Order No.	2004970000
Version	THM, Conductor and cable markers, 8 - 23 mm, 25.4 x 100 mm, white
GTIN (EAN)	4050118415391
Qty.	2,000 pc(s).
compatible printer	2430920000 2448870000

THM

THM WO 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	100 mm	Width (inches)	3.937 inch
Height	25.4 mm	Height (inches)	1 inch
Depth	0.025 mm	Depth (inches)	0.001 inch
Net weight	0.406 g		

General data

Adhesive	Polyacrylate adhesive	Colour	white
Halogen	No	Material	Polyester film
Number per roll	2,000	Operating temperature range	-40...150 °C
Size of labelling field	24.5 x 25 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Width	100 mm

Conductor and cable markers

Conductor O.D.	8 - 23 mm	Conductor O.D., max.	23 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Halogen	No

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
------------------	-----------------------