

**A-series
APGLE 1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	APGLE 1.5
Order No.	2482720000
GTIN (EAN)	4050118496253
Qty.	25 pc(s).

**A-series
APGLE 1.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Dimensions and weights**

Width	2.35 mm	Width (inches)	0.093 inch
Height	5.78 mm	Height (inches)	0.228 inch
Depth	24.1 mm	Depth (inches)	0.949 inch
Net weight	0.149 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Colour	orange
--------	--------

Classifications

ETIM 6.0	EC002848	eClass 6.2	27-14-92-14
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Engineering Data	STEP

A-series APGLE 1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

