

ELS
ELS 16/40 K MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



ELS MultiCard markers can be printed with a PrintJet, plotter or SMark printer. In particular, colour printing with PrintJet AVANCED allows the eye-catching identification marking of cables and terminal strips in many ways.

ELS 6/30 for use in the WKM 8/30 cable markers or in the EM8/30 group-tag carriers

ELS 7/40 for use in the SchT5S group-tag carriers

ELS 16/40 for use in the WKM 18/43 cable markers or the SchT5 group-tag carriers

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ELS 16/40 K MC NE WS
Order No.	1411800000
Version	ELS, Insert markers, 40 x 16 mm, white
GTIN (EAN)	4050118212563
Qty.	40 pc(s).
compatible printer	1324380000

ELS ELS 16/40 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	16 mm	Width (inches)	0.63 inch
Height	40 mm	Height (inches)	1.575 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	2.8 g		

General data

Colour	white	Halogen	No
Material	Polyamide 66	Number per sheet	8
Operating temperature range	-40...100 °C	UL 94 flammability rating	V-2
Width	16 mm		

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

ELS **ELS 16/40 K MC NE WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

