

cable lug, terminal end KQI-M10/-6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	KQI-M10/-6
Order No.	1492410000
Version	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6 mm ²
GTIN (EAN)	4050118302363
Qty.	100 pc(s).

cable lug, terminal end KQI-M10/-6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	2.85 g
------------	--------

Connectors

Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Connection length (l)	28 mm	Hole	M10
Identification colour	yellow	Inside diameter of collar (d4)	6.4 mm
Inside diameter of flange (d2)	10.5 mm	Inside diameter of shaft (d1)	3.6 mm
Material/plastic	PC	Outside diameter of shaft (d3)	18 mm

Classifications

ETIM 5.0	EC001059	ETIM 6.0	EC001059
eClass 6.2	27-40-02-90	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-40-02-12
eClass 9.1	27-40-02-12		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end KQI-M10/-6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

