

## PAC PAC-CTLX-UNIU-V1-2M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

### General ordering data

|            |  |
|------------|--|
| Type       | PAC-CTLX-UNIU-V1-2M  |
| Order No.  | <a href="#">7789733020</a>                                 |
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| GTIN (EAN) | 4032248343331  |
| Qty.       | 1 pc(s).   |

## Data sheet

### PAC PAC-CTLX-UNIU-V1-2M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 490 g |
|------------|-------|

### Temperatures

|                             |             |                             |             |
|-----------------------------|-------------|-----------------------------|-------------|
| Operating temperature, max. | 50 °C       | Operating temperature, min. | -10 °C      |
| Storage temperature, max.   | 60 °C       | Storage temperature, min.   | -10 °C      |
| Operating temperature       | -10...50 °C | Storage temperature         | -10...60 °C |

### General Data

|                       |                                      |                     |  |
|-----------------------|--------------------------------------|---------------------|--|
| Connector PLC side    | ROCKWELL CONTROL LOGIX 1756-TBCH 36P | Interface connector | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) |
| Number of poles, min. | 36-pole                              | Outer diameter      | 11.7 ± 1 mm                              |
| Cable                 | Cable LiYY                           | Cable length        | 2 m                                      |
| Material              | PVC                                  | Wire cross-section  | 0.25 mm <sup>2</sup>                     |

### Electrical Data

|                      |                     |   |           |
|----------------------|---------------------|---|-----------|
| Rated voltage (text) | ≤ 250 Vdc ≤ 250 Vac | Permissible current strength per path, max. | 1 A       |
| Total current, max.  | 3 A                 | Resistance                                  | ≤ 80 mΩ/m |
| High voltage test    | 1 KV/1s             |   |           |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC000237    | ETIM 6.0   | EC000237    |
| eClass 6.2 | 27-24-92-05 | eClass 7.1 | 27-24-92-05 |
| eClass 8.1 | 27-24-92-05 | eClass 9.0 | 27-24-22-20 |
| eClass 9.1 | 27-24-22-20 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                               |
|--------------------|-------------------------------|
| User Documentation | <a href="#">Colours chart</a> |
|--------------------|-------------------------------|