

## ESG ESG 9/17 K MC NE BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

### General ordering data

|                    |   |
|--------------------|---|
| Type               | ESG 9/17 K MC NE BL   |
| Order No.          | <a href="#">1208960000</a>                                      |
| Version            | ESG, Device markers x 17 mm, PA 66, Colour: blue, Self-adhesive |
| GTIN (EAN)         | 4032248990351   |
| Qty.               | 200 pc(s).  |
| compatible printer | <a href="#">1324380000</a>                                      |

## Data sheet

**ESG**  
**ESG 9/17 K MC NE BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 17 mm  | Width (inches)  | 0.669 inch |
| Height     | 9 mm   | Height (inches) | 0.354 inch |
| Depth      | 0.8 mm | Depth (inches)  | 0.031 inch |
| Net weight | 0.55 g |                 |            |

### General data

|                             |                            |                           |               |
|-----------------------------|----------------------------|---------------------------|---------------|
| Adhesive                    | Double-sided adhesive tape | Application/manufacturer  | Self-adhesive |
| Colour                      | blue                       | Halogen                   | No            |
| Material                    | PA 66                      | Number per sheet          | 40            |
| Operating temperature range | -40...100 °C               | UL 94 flammability rating | V-2           |
| Version                     | Self-adhesive              | Width                     | 17 mm         |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC001288    | eClass 6.2 | 27-14-91-29 |
| eClass 9.0 | 27-40-06-29 | eClass 9.1 | 27-40-06-29 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
| Engineering Data | <a href="#">STEP</a>         |

**Data sheet**

**ESG**  
**ESG 9/17 K MC NE BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

