

THM
THM EL VIN 15 WS 2L 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

General ordering data

Type	THM EL VIN 15 WS 2L 30M
Order No.	1307670000
Version	THM, Device markers, 15, white
GTIN (EAN)	4050118109870
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM

THM EL VIN 15 WS 2L 30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	239 g		

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Length	30,000 mm	Material	Vinyl film
Number per roll	1	Number per sheet	1
Operating temperature range	-40...80 °C	Printing method	Thermotransfer
UL 94 flammability rating	HB	Version	Endless, Self-adhesive

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

THM THM EL VIN 15 WS 2L 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

