

**PROtop
PRO COM CAN OPEN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Power supplies from Weidmüller have long since proved their worth in supplying electrical modules.

They can therefore be used safely in harsh industrial environments, in small businesses and in living areas, and have been granted international approvals. Weidmüller provides power supplies and additional components for industrial applications:

- Switched-mode power supply units
- DC/DC converters
- UPS control modules
- Electronic fuses

General ordering data

Type	PRO COM CAN OPEN
Order No.	2467320000
Version	
GTIN (EAN)	4050118482225
Qty.	1 pc(s).

**PROtop
PRO COM CAN OPEN**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	35 mm	Width (inches)	1.378 inch
Height	74.4 mm	Height (inches)	2.929 inch
Depth	33.6 mm	Depth (inches)	1.323 inch
Weight	36 g	Net weight	76 g

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-25 °C
Operating temperature	-25 °C...70 °C	Storage temperature	

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Operating temperature	-25 °C...70 °C	Protection degree	IP20
Weight	36 g		

System data

Connection type	2 x RJ45 plug-in connectors	Field bus protocol	CANopen
Interface	PROtop interconnection interface	Module type	plug-on module

Classifications

ETIM 6.0	EC001604	eClass 6.2	27-04-90-04
eClass 9.0	27-24-26-08	eClass 9.1	27-04-07-92

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity DE_PA5600_180206_001.pdf
Engineering Data	STEP
Software	EDS File