THM
THM EL VIN 100 WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Customised identification: EL
The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

General ordering data

Type	THM EL VIN 100 WS 30M
Order No.	2518700000
Version	THM, Device markers, 100, white
GTIN (EAN)	4050118541281
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM
THM EL VIN 100 WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Height	100 mm	Height (inches)	3.937 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	500 g		

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Length	30,000 mm	Material	Vinyl film
Number per roll	1	Number per sheet	1
Printing method	Thermotransfer	UL 94 flammability rating	HB
Version	Endless, Self-adhesive		

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN

THM
THM EL VIN 100 WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings