

**Industrial Ethernet  
IE-PS-V14M-2SC-POF-QA**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



PushPull plug-in connector set according to IEC  
61076-3-117 ver.14 (PROFINET), metal incl. SC insert

**General ordering data**

Type	IE-PS-V14M-2SC-POF-QA
Order No.	<a href="#">2568260000</a>
Version	FO connector, Version 14, SC-RJ POF, IP67
GTIN (EAN)	4050118578928
Qty.	10 pc(s).

**Industrial Ethernet  
IE-PS-V14M-2SC-POF-QA**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight	55.44 g
------------	---------

**Temperatures**

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**General data**

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	Rapid connection system: screwing, cutting	Description of article	Version 14, SC-RJ POF
Fibre type	POF	Housing main material	Zinc diecast
Housing material, insert	PA, Zinc diecast	Insertion loss	≤ 1.0 dB
Plugging cycles	750	Protection degree	IP67
Sheath diameter, max.	10 mm	Sheath diameter, min.	5 mm

**Standards**

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

**Classifications**

ETIM 6.0	EC001122	eClass 6.2	27-26-07-08
eClass 9.0	19-17-01-22	eClass 9.1	19-07-01-22

**Approvals**

ROHS	Conform
------	---------