

**CRIMPFIX LS PZ3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Type	CRIMPFIX LS PZ3
Order No.	<a href="#">9025300000</a>
Version	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4008190380335
Qty.	1 pc(s).

**CRIMPFIX LS PZ3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Width	390 mm	Width (inches)	15.354 inch
Height	460 mm	Height (inches)	18.11 inch
Depth	330 mm	Depth (inches)	12.992 inch
Weight	31 kg	Net weight	35,000 g

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Technical data**

Electrical connection	100-240 V / 50/65 Hz
-----------------------	----------------------

**PW65 maintenance - automatic stripping/crimping**

Compressed-air connection	5 bar	Consumables	loose wire-end ferrules
Crimping length	6/8/10 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/65 Hz	Length of wire-end ferrule	12/14/16 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm <sup>2</sup>
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC002778	eClass 6.2	17-13-01-01
eClass 9.0	17-13-01-01	eClass 9.1	17-13-01-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Manual</a>
--------------------	------------------------