

SAIE-M12S-4-0.2U P9 .75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIE-M12S-4-0.2U P9 .75
Order No.	1353770000
Version	Built-in plugs, M12, pin, straight, PG 9, No. of poles: 4
GTIN (EAN)	4050118156195
Qty.	1 pc(s).

SAIE-M12S-4-0.2U P9 .75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 21 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Standards

Connector standard IEC 61076-2-101

General data

Cable glands	PG 9	Coding	A
Conductor O.D.	-	Connection thread	M12
Contact surface	Gold-plated	Core cross-section	18 AWG
Housing main material	Brass, nickel-plated	No. of poles	4
Protection degree	IP67, when screwed in	Rated current	8 A
Rated current	Contacts 1-4 8A, contact 5 2A	Rated voltage	250 V
Strand / cable length	0.2 m	Temperature range of housing	-40 ... +85 °C

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002635
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

Approvals

Approvals



ROHS Conform

Downloads
 Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)

SAIE-M12S-4-0.2U P9 .75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Drawings****Pole scheme**