

**Cabtite (cable entry system)
CABTITE GI I BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The pluggable click inlays allow the frame openings to be configured as required for use with small or large sealing elements. An audible "click" confirms correct installation. This means that the Cabtite cable entry system can be variably configured for different requirements (cables, conductors, hoses, pneumatic and hydraulic lines).

General ordering data

Type	CABTITE GI I BK
Order No.	2584320000
Version	grid inlay, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 17.5 mm, Width: 5 mm, Depth: 17.5 mm, -40 °C...120 °C
GTIN (EAN)	4050118616071
Qty.	5 pc(s).

Cabtite (cable entry system) CABTITE GI I BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	44 mm	Length (inches)	1.732 inch
Width	5 mm	Width (inches)	0.197 inch
Height	17.5 mm	Height (inches)	0.689 inch
Height of lowest version	17.5 mm	Depth	17.5 mm
Depth (inches)	0.689 inch	Net weight	2.7 g

General information

UL 94 flammability rating	V-0	Halogen	No
Silicone	No	Sealing	TPE
Material	Polyamide, glass fibre-reinforced		

Classifications

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	STEP
User Documentation	Cabtite Installation Instructions