

**Z-series
ZQV 6/2 GE ZTL6**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	ZQV 6/2 GE ZTL6
Order No.	1363010000
Version	Z-series, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4050118165456
Qty.	60 pc(s).

Z-series ZQV 6/2 GE ZTL6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	3.1 mm	Width (inches)	0.122 inch
Height	14.3 mm	Height (inches)	0.563 inch
Depth	33.96 mm	Depth (inches)	1.337 inch
Net weight	2.72 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

Dimensions

Pitch in mm (P)	8.1 mm
-----------------	--------

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 3.0	EC000489	ETIM 5.0	EC000489
ETIM 6.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40	eClass 8.1	27-14-11-40
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------