

**Connecting elements**  
**H1,5/14D SW SP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Polypropylene conical cable entry funnel
- Heat-resistant up to 105°C
- Entry funnel can also be manufactured from a non-flammable material on request

For conductors from 0.14 – 150 mm<sup>2</sup> (AWG 26-300 MCM)

Material: E-Cu, tin galvanised

Dimensional tolerance acc. to DIN 46228 sect. 4

**General ordering data**

Type	H1,5/14D SW SP
Order No.	<a href="#">1476330000</a>
Version	Wire-end ferrule, insulated, 10 mm, 8 mm, black
GTIN (EAN)	4050118283075
Qty.	100 pc(s).

**Connecting elements  
H1,5/14D SW SP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	14 mm	Width (inches)	0.551 inch
Net weight	0.12 g		

**Technical data**

Version	insulated
---------	-----------

**Wire-end ferrules**

Collar diameter (D2)	3.5 mm	Colour code	DIN
Conductor cross-section	1.5 mm <sup>2</sup>	Contact surface diameter (D1)	1.7 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 012 A
Plastic collar thickness (S2)	0.25 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 16		

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01	eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN</a>
------------------	-----------------------