

cable lug, terminal end KQI-M10/-10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	KQI-M10/-10
Order No.	1492470000
Version	cable lug, terminal end, Insulated cable connector, 10 mm ²
GTIN (EAN)	4050118302233
Qty.	50 pc(s).

cable lug, terminal end KQI-M10/-10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	4 g
------------	-----

Connectors

Conductor cross-section	10 mm ²	Connection length (l)	29.5 mm
Hole	M10	Identification colour	red
Inside diameter of collar (d4)	8 mm	Inside diameter of flange (d2)	10.5 mm
Inside diameter of shaft (d1)	4.5 mm	Material/plastic	PA
Outside diameter of shaft (d3)	18 mm		

Classifications

ETIM 5.0	EC001059	ETIM 6.0	EC001059
eClass 6.2	27-40-02-90	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-40-02-12
eClass 9.1	27-40-02-12		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end KQI-M10/-10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

