

**A-series  
APGLE 2.5/4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

| Type       | APGLE 2.5/4                |
|------------|----------------------------|
| Order No.  | <a href="#">2457570000</a> |
| GTIN (EAN) | 4050118473100              |
| Qty.       | 25 pc(s).                  |

**A-series**  
**APGLE 2.5/4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 3.9 mm   | Width (inches)  | 0.154 inch |
| Height     | 5.68 mm  | Height (inches) | 0.224 inch |
| Depth      | 31.35 mm | Depth (inches)  | 1.234 inch |
| Net weight | 0.368 g  |                 |            |

**Temperatures**

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C        |                                  |        |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC002848    | eClass 6.2 | 27-14-92-14 |
| eClass 9.0 | 27-14-11-92 | eClass 9.1 | 27-14-11-92 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                          |
|--------------------|------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>      |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |

### A-series APGLE 2.5/4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

