

A-series
APGSR 2.5/4 - 8P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	APGSR 2.5/4 - 8P
Order No.	2457600000
GTIN (EAN)	4050118472929
Qty.	25 pc(s).

A-series
APGSR 2.5/4 - 8P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	30.1 mm	Width (inches)	1.185 inch
Height	7.87 mm	Height (inches)	0.31 inch
Depth	53 mm	Depth (inches)	2.087 inch
Net weight	4.36 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	orange
----------	-------	--------	--------

Classifications

ETIM 6.0	EC002848	eClass 6.2	27-14-92-14
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

A-series APGSR 2.5/4 - 8P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

