

RKDG D18 WG PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Extensive range of accessories for the FieldPower® boxes.

Cable seals, plug-in connectors, locking elements and much more.

General ordering data

Type	RKDG D18 WG PT6
Order No.	2491870000
Version	FieldPower®, Sealing insert, round, IP54, 18.5 - 20.5 mm
GTIN (EAN)	4050118501537
Qty.	10 pc(s).

RKDG D18 WG PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	21.8 g
------------	--------

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

General data

Clamping range, max.	20.5 mm	Clamping range, min.	18.5 mm
Colour	black	Halogen	No
Line type	round	Material	EPDM
Protection degree	IP54	Silicone-free	Yes
Thickness	18 mm		

Classifications

ETIM 6.0	EC002498	eClass 6.2	23-07-16-90
eClass 9.0	27-14-11-92	eClass 9.1	27-14-25-90

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------