






Denver NVI-450

- Digital night vision monocular with video recorder/photo function
- 5 x fixed optical zoom + 5 x digital zoom
- Range from 5 meters up to 200 meters - also at night
- Built-in adjustable LED IR light with wavelength: 940nm
- 40mm lens and 1.3MP CCD sensor
- Field of view: 7.6 degrees
- Diopter adjustment: +/- 0,6D
- Pixel: 1.3Mega Pixel for digital camera 1280x960 resolution
- Video recorder function/ Video resolution: 640x480 / 15fps
- Needs MicroSD card to take photos and record video (not included)
- Built in LCD display: 1.3inch LCD panel
- Rechargeable battery included
- AV output for connection to TV

Accessories included: 1 x lithium rechargeable battery, AC/DC adaptor with USB output, black carry bag incl. strap, black pouch for holding accessories, polishing cloth, AV cable, USB to mini USB cable, round DC jack to USB cable, Manual, Rubber protection for lense



-  HIGHLIGHTS
Digital night vision monocular with video recorder/photo function, 5 x optical zoom
-  POWER
230V~50Hz AC/DC adaptor
-  BATTERY
Rechargeable battery included
-  CAMERA
1.3Mpixel - Photo up to 1280x960, video VGA 640x480@15FPS
-  CONNECTIONS
AV output for connection with TV

Shipping information

Unit size: 8.60(w) x 20.00(d) x 5.60(h) cm

Unit weight: 0.75

Giftbox size: 7.50(w) x 14.00(d) x 22.50(h) cm

4 pcs./export carton

3800 pcs./20' container

8800 pcs./40' HQ container

Barcode: 5706751043178