

Data Sheet

Multi-core speaker cable

b/n	Color	Length	b/n	Color	Length
1953901	White	100 M	1953913	White	25 M
1935902	Black	100 M	1953915	Black	25 M
1953903	Brown	100 M	1953916	Brown	25 M
1953904	Grey	100 M	1953917	Grey	25 M
1953907	White	10 M	1953919	White	50 M
1953909	Black	10 M	1953921	Black	50 M
1953910	Brown	10 M	1953922	Brown	50 M
1953911	Grey	10 M	1953923	Grey	50 M

Conductor: Bare Copper

Cross section: 0.34 mm²

Construction: 0.25mm x 7

Insulation: PVC

Insulation OD: 1.8mm x 3.6mm

Rating Voltage: below 50 V/DC

Insulating Resistance: Min. 100mΩ/ 500V/ DC

Operating Temperature: -20°C to 70°C