

Data Sheet

Multi-core Speaker Cable

b/n	Color	Length	b/n	Color	Length
1953905	Transparent	100 M	1953914	Grey	25 M
1935906	Grey	100 M	1953918	Transparent	25 M
1953908	Grey	10 M	1953920	Grey	50 M
1953912	Transparent	10 M	1953924	Transparent	50 M

Conductor: Bare Copper

Cross section: 0.40 mm²

Construction: 0.2mm x 13

Insulation: PVC

Insulation OD: 2 mm x 4 mm

Rating Voltage: below 50 V/DC

Insulating Resistance: Min. 100mΩ/ 500V/ DC

Operating Temperature: -20°C to 70°C