

APG 10 L (785 810)

- Excellent fit due to special glove cut
- Good touch sensitivity due to soft leather glove palm
- Breathable materials maximise wearing comfort



Figure without obligation

Type	APG 10 L
Part No.	785 810
Direct incident energy (E_{io})	(class 2 / 7 kA, 500 ms) 423 kJ / m ²
Extended direct incident energy (E_{io})	(class 2*) 1050 ... 1390 kJ / m ²
Arc energy (W_{arc})	318 kJ
ATPV (Arc Thermal Performance Value)	32.8 cal / cm ²
Total length	450 mm
Gauntlet length	230 mm
Size (international)	10 (XL)
Material (glove palm)	Siliconised calf grain leather
Material (glove back)	100% Kevlar® interlock knit
Material (sewing thread)	Kevlar®
Standard	Box test according to IEC 61482-1-2, ATPV test according to IEC 61482-1-1, DIN EN 388, DIN EN 407
Weight	290 g/Pa
Customs tariff number (Comb. Nomenclature EU)	42032910
GTIN	4013364242302
PU	1 Pa

*) The distance of the specimen was reduced from 300 mm to 150 mm based on IEC 61482-1-2.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.