

## APG 10 (785 798)

- Excellent fit due to special glove cut
- Good touch sensitivity due to soft leather glove palm
- Breathable materials maximise wearing comfort



Figure without obligation



Figure without obligation

Type Part No.	APG 10 785 798
Direct incident energy ( $E_{ic}$ )	(class 2 / 7 kA, 500 ms) 423 kJ / m <sup>2</sup>
Extended direct incident energy ( $E_{ie}$ )	(class 2*) 1050 ... 1390 kJ / m <sup>2</sup>
Arc energy ( $W_{arc}$ )	318 kJ
ATPV (Arc Thermal Performance Value)	32.8 cal / cm <sup>2</sup>
Total length	330 mm
Gauntlet length	100 mm
Size (international)	10 (XL)
Material (glove palm)	Siliconised calf grain leather
Material (glove back)	100% Kevlar® interlock knit
Material (sewing thread)	Kevlar®
Standard	Box test in accordance with IEC 61482-1-2, ATPV test in accordance with IEC 61482-1-1, DIN EN 388, DIN EN 407
Weight	180 g/Pa
Customs tariff number (Comb. Nomenclature EU)	42032910
GTIN	4013364124943
PU	1 Pa

\*<sup>1</sup>) The distance of the specimen was reduced from 300 mm to 150 mm based on IEC 61482-1-2.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.