


TE 20 1500 Z STTZN (620 151)



Figure without obligation



Type	TE 20 1500 Z STTZN
Part No.	620 151
Material	St/tZn
Rod length (l1)	1500 mm
Diameter Ø (d1)	20 mm
Pin diameter	12 mm
Hot-dip galvanisation - single value:	~70 µm
Hot-dip galvanisation - average value:	≥ 55 µm
Tensile strength	410 N/mm ²
Static tensile strength (vertical tension)	approx. 22000 N
Specific conductivity	≥ 6.66 m/Ohm mm ²
Specific resistance	≤ 0.15 Ohm mm ² / m
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	7.9 kA
Standard	EN 62561-2
Weight	3,7 kg
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364021846
PU	6 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.