

Data Sheet

118pcs Transparent 3:1 adhesive lined heat shrink tube - assortment

This range of heat shrink tube are particularly suitable for hobbyists, craftsmen, field service, service workshops, laboratory, and the cable repairing needs.
118 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm. Hot-melt adhesive lined tubing in the transparent color.



3:1 Adhesive Lined Heat Shrink Tube

Inner diameter \varnothing	After shrinking \varnothing	Tube length	Color	Quantity
1.6 mm	0.5 mm	32 mm	Transparent	35 pcs
2.4 mm	0.8 mm	32 mm	Transparent	25 pcs
3.2 mm	1.0 mm	32 mm	Transparent	20 pcs
4.8 mm	1.6 mm	65 mm	Transparent	15 pcs
6.4 mm	2.2 mm	65 mm	Transparent	8 pcs
7.9 mm	2.7 mm	65 mm	Transparent	5 pcs
9.5 mm	3.2 mm	95 mm	Transparent	4 pcs
12.7 mm	4.2 mm	95 mm	Transparent	6 pcs

Operating Temperature: -45 ~110°C
Minimum shrink temperature: 90°C
Full recovery temperature: 125°C