

## Data Sheet

# 3:1 Heat shrinking adhesive lined tube pack


Material: Polyethylene(PE)

Shrinking ratio: 3:1

Operating Temperature: -45 ~110°C

Minimum shrink temperature: 90°C

Full recovery temperature: 125°C



| Type number | Diameter D ø | Diameter dø | Colour      | Pack contents  |
|-------------|--------------|-------------|-------------|----------------|
| T1902CA020  | 1.5 mm       | 0.5 mm      | Blue        | 15pcs x 150 mm |
| T1902CA021  | 1.5 mm       | 0.5 mm      | Brown       | 15pcs x 150 mm |
| T1902CA022  | 1.5 mm       | 0.5 mm      | Grey        | 15pcs x 150 mm |
| T1902CA023  | 1.5 mm       | 0,5 mm      | Red         | 15pcs x 150 mm |
| T1902CA024  | 1.5 mm       | 0.5 mm      | Transparent | 15pcs x 150 mm |
| T1902CA025  | 1.5 mm       | 0.5 mm      | Black       | 15pcs x 150 mm |
| T1902CA026  | 3.0 mm       | 1.5 mm      | Blue        | 15pcs x 150 mm |
| T1902CA027  | 3.0 mm       | 1.5 mm      | Brown       | 15pcs x 150 mm |
| T1902CA028  | 3.0 mm       | 1.5 mm      | Grey        | 15pcs x 150 mm |
| T1902CA029  | 3.0 mm       | 1.5 mm      | Red         | 15pcs x 150 mm |
| T1902CA030  | 3.0 mm       | 1.5 mm      | Transparent | 15pcs x 150 mm |
| T1902CA031  | 3.0 mm       | 1.5 mm      | Black       | 15pcs x 150 mm |
| T1902CA032  | 6.0 mm       | 2.0 mm      | Black       | 15pcs x 150 mm |
| T1902CA033  | 6.0 mm       | 2.0 mm      | Blue        | 15pcs x 150 mm |
| T1902CA034  | 6.0 mm       | 2.0 mm      | Brown       | 15pcs x 150 mm |
| T1902CA035  | 6.0 mm       | 2.0 mm      | Grey        | 15pcs x 150 mm |
| T1902CA036  | 6.0 mm       | 2.0 mm      | Red         | 15pcs x 150 mm |
| T1902CA037  | 6.0 mm       | 2.0 mm      | Transparent | 15pcs x 150 mm |
| T1902CA038  | 12.0 mm      | 4.0 mm      | Blue        | 15pcs x 150 mm |
| T1902CA039  | 12.0 mm      | 4.0 mm      | Brown       | 15pcs x 150 mm |
| T1902CA040  | 12.0 mm      | 4.0 mm      | Grey        | 15pcs x 150 mm |
| T1902CA041  | 12.0 mm      | 4.0 mm      | Red         | 15pcs x 150 mm |
| T1902CA042  | 12.0 mm      | 4.0 mm      | Transparent | 15pcs x 150 mm |
| T1902CA043  | 12.0 mm      | 4.0 mm      | Black       | 15pcs x 150 mm |