

## Data Sheet

### 300pcs Transparent 3:1 adhesive lined heat shrink tube - assortment

This range of heat shrink tube are particularly suitable for hobbyists, craftsmen, field service, service workshops, laboratory, and the cable repairing needs.  
300 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm.  
Hot-melt adhesive lined tubing in the transparent color.



#### 3:1 Adhesive Lined Heat Shrink Tube

Inner diameter $\varnothing$	After shrinking $\varnothing$	Tube length	Color	Quantity
1.6 mm	0.5 mm	60 mm	Transparent	100 pcs
2.4 mm	0.8 mm	60 mm	Transparent	70 pcs
3.2 mm	1.0 mm	60 mm	Transparent	50 pcs
4.8 mm	1.6 mm	60 mm	Transparent	30 pcs
6.4 mm	2.2 mm	60 mm	Transparent	20 pcs
7.9 mm	2.7 mm	60 mm	Transparent	10 pcs
9.5 mm	3.2 mm	60 mm	Transparent	10 pcs
12.7 mm	4.2 mm	60 mm	Transparent	10 pcs

Operating Temperature: -45 ~110°C

Minimum shrink temperature: 90°C

Full recovery temperature: 125°C