

Data Sheet

DIN EN 60445 (VDE 0197) color codes heat shrinking tube assortment pack

Designed for DC application use 


Material: Polyethylene(PE)

Shrinking ratio: 3:1 / 2:1

Operating Temperature: -45 ~110°C

Minimum shrink temperature: 90°C

Full recovery temperature: 125°C



Diameter Dø	Diameter dø	Colour	Shrinking ratio	Pack contents
1.6 mm	0.5 mm	Red	3 : 1	1pc x 150 mm
1.6 mm	0.5 mm	White	3 : 1	1pc x 150 mm
1.6 mm	0.5 mm	Black	3 : 1	1pc x 150 mm
1.6 mm	0,8 mm	Green/Yellow	2 : 1	1pc x 150 mm
2.4 mm	0.8 mm	Red	3 : 1	1pc x 150 mm
2.4 mm	0.8 mm	White	3 : 1	1pc x 150 mm
2.4 mm	0.8 mm	Black	3 : 1	1pc x 150 mm
2.4 mm	1.2 mm	Green/Yellow	2 : 1	1pc x 150 mm
3.2 mm	1.0 mm	Red	3 : 1	2pcs x 150 mm
3.2 mm	1.0 mm	White	3 : 1	2pcs x 150 mm
3.2 mm	1.0 mm	Black	3 : 1	2pcs x 150 mm
3.2 mm	1.6 mm	Green/Yellow	2 : 1	2pcs x 150 mm
4.8 mm	1.6 mm	Red	3 : 1	1pc x 150 mm
4.8 mm	1.6 mm	Black	3 : 1	1pc x 150 mm
4.8 mm	1.6 mm	White	3 : 1	1pc x 150 mm
4.8 mm	2.4 mm	Green/Yellow	2 : 1	1pc x 150 mm

* 3:1 shrinking ratio tube are with an inner adhesive glue