

## Han 3A-AK-DICHTUNG SCHWARZ



Part number	09 20 003 5409
Specification	Han 3A-AK-DICHTUNG SCHWARZ
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035409">https://b2b.harting.com/09200035409</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/ housing	for bulkhead mounted housings
	for surface mounted housings
	Thermoplastic With seal

### Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert or for mounted Han-Brid® insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
----------------	----

Net weight	5 g
------------	-----

Country of origin	Romania
-------------------	---------

Customs tariff number	85389099
-----------------------	----------