

Han 3A-AK-QB-Dichtung



Part number	09 20 003 5421
Specification	Han 3A-AK-QB-Dichtung
HARTING eCatalogue	https://b2b.harting.com/09200035421

Identification

Category	Hoods/Housings
Series of hoods/housings Han A [®]	
Type of hood/housing	Protection cover
Description of hood/ housing	for hoods
	Metal
	With fixing cord
	With seal

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 $\%$ lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Material properties

|--|

Specifications and approvals

Approvals	DNV GL	
-----------	--------	--

Commercial data

Packaging size	10
Net weight	30.72 g
Country of origin	Germany
Customs tariff number	85389099