

## Han 3A-AK



Part number	09 20 003 5428
Specification	Han 3A-AK
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035428">https://b2b.harting.com/09200035428</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/ housing	for cable to cable housing Metal With fixing cord

### Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Approvals	DNV GL
-----------	--------

### Commercial data

Packaging size	10
----------------	----



Pushing Performance

## Commercial data

Net weight 22.6 g

Country of origin Germany

Customs tariff number 85389099