

# Han 3A-C/P-f.Hood-DL-seal-grey-w.cord



Part number	09 20 003 5441
Specification	Han 3A-C/P-f.Hood-DL-seal-grey-w.cord
HARTING eCatalogue	https://b2b.harting.com/09200035441

#### Identification

Category	Hoods/Housings
Series of hoods/housing	SHan A <sup>®</sup>
Type of hood/housing	Protection cover
	for hoods
Description of hood/	for hoods Thermoplastic
Description of hood/ housing	101 110000

#### Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert or for mounted Han-Brid <sup>®</sup> insert

### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (seal)	NBR
Material (locking)	Polyamide
Colour (locking)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

	Approvals	DNV GL	
--	-----------	--------	--

## Commercial data

Packaging size	10
Net weight	10.36 g
Country of origin	Romania
Customs tariff number	85389099