

## Han 16A-AK-LB (Schnur fuer Pg16)



Part number	09 20 016 5423
Specification	Han 16A-AK-LB (Schnur fuer Pg16)
HARTING eCatalogue	<a href="https://b2b.harting.com/09200165423">https://b2b.harting.com/09200165423</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/housing	for hoods Metal With fixing cord
Type	Low construction High construction

### Version

Locking type	Single locking lever
Han-Easy Lock®	Yes
Size	16 A
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Surface (hood/housing)	Powder-coated
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	83.8 g
Country of origin	Germany
Customs tariff number	85389099