

## Han A PROTECT COVER 4 PEGS



Part number	09 20 032 5405
Specification	Han A PROTECT COVER 4 PEGS
HARTING eCatalogue	<a href="https://b2b.harting.com/09200325405">https://b2b.harting.com/09200325405</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Metal
Type	Low construction High construction

### Version

Locking type	Double locking lever
Size	32 A
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Surface (hood/housing)	Powder-coated
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	31.8 g
Country of origin	Germany
Customs tariff number	85389099