

Han 10B-cover-cord-thermoplast. f Termin



Part number	09 30 010 5412
Specification	Han 10B-cover-cord-thermoplast. f Termin
HARTING eCatalogue	https://b2b.harting.com/09300105412

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Thermoplastic
	With fixing cord
Type	Low construction
	High construction

Version

Locking type	Single locking lever
Size	10 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	22.6 g
Country of origin	Germany
Customs tariff number	85389099
